



Transformer, dry type, encapsulated, 15kVA, 3 phase, 480V delta primary, 208Y/120V secondary, 14C, 115C rise

15T2FSS

Main

Product Or Component Type	Dry Sealed Transformer	
Primary To Secondary Voltage	480 V delta 208Y/120 V	
Full Capacity Taps	2 5 % FCBN	

Complementary

Enclosure Code	14C	
Phase	3 phases	
Power Rating	15 kVA	
Temperature Rise	115 °C	
Height	14.75 in (374.65 mm)	
Width	19.1 in (485.14 mm)	
Depth	12.25 in (311.15 mm)	
Enclosure Mounting	Wall mounted	
Enclosure Material	Stainless steel	

Environment

Enclosure Type	NEMA 3R
Insulation Temperature	356 °F (180 °C)
Product Certifications	CSA UL listed
	cULus

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	14.10 in (35.814 cm)	
Package 1 Width	15.30 in (38.862 cm)	
Package 1 Length	19.10 in (48.514 cm)	
Package 1 Weight	335.00 lb(US) (151.953 kg)	

Contractual warranty

warranty	18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information Yes	
Ø	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations