

Waterproof USB Type C

WITH IPX8 AND SUPPORTS USB 2.0,USB 3.2 GEN 1,USB 3.2 GEN 2 AND USB 4

The usability of Waterproof Type C is with strong IP performance and unique IP technology to ensure each part meets the high quality of waterproof performance.

- IPX8 Waterproof
- High-speed transmission up to 40Gb/s super speed
- Power rating up to 240W
- Optimized contact design for superior signal integrity performance
- Reversible plug and cable orientation



FEATURES

- Unique Liquid silicone rubber technology
- Support a variety of USB protocols
- High power and fast charging
- Mid-plate tongue design
- Unique O-ring technology (LIM) for waterproof
- All-in-one simplicity

BENEFITS

- Offers superior bonding with outer shell to prevent water ingression
- Offers product portfolio for USB 2.0, USB 3.2 Gen 1, USB 3.2 Gen 2,USB 4 products
- Extended 5A current rating for USB power delivery and up to 240W
- Ensure high reliability while preventing damage from connector mishandling
- Reach IPX4 ~ X8 rating
- Support power delivery, data transfer, video output in one connector

TECHNICAL INFORMATION

MATERIAL

■ Housing: LCP UL94-V0

• Molding Housing: Black, High temperature plastic

• Top Terminal: Copper Alloy

• Bottom Terminal: Copper Alloy

Mid Plate: Stainless Steel
 Outer Shell: Stainless Steel
 Main Shell: Stainless Steel

• Small Shell: Stainless Steel

MECHANICAL PERFORMANCE

Durability: 10000 cyclesInsertion Force: 5~20N

■ Extraction Force: 8~20N

ELECTRICAL PERFORMANCE

• Low Level Contact Resistance: $40m\Omega$ max.

• Insulation Resistance: $100m\Omega$ min.

• Contact Current Rating: 5A max.

• Dielectric Withstanding Voltage: 100VAC

PACKAGING

■ Tape & Reel

SPECIFICATION

Amphenol Product Specification

APPROVALS AND CERTIFICATIONS

RoHS

Halogen-free

ENVIRONMENTAL

■ Operating Temperature Range: -40°C to +85°C

TARGET MARKETS/APPLICATIONS



Automotive Infotainment



Notebook
Docking
Tablet
Parish arals (Manitar (D

Peripherals (Monitor/Display, Projector...) Home Entertainment



Storage

PART NUMBERS

Description	Part Numbers
USB 4 Gen 3, Type C, Receptacle, R/A, Mid mount, Center Height 0.4mm, Dual Row SMT, IPX8	12402060E512A
USB 4 Gen 3, Type C, Receptacle, R/A, Mid mount, Center Height 0.4mm, Dual Row SMT, IPX8	12402136E512A
USB 4 Gen 3, Type C, Vertical, Length 7.5mm, Dual Row SMT, IPX8	2402082E512A
USB 3.2 Gen 1, Type C, Receptacle, R/A, Top mount, Center Height 1.5mm, Dual Row SMT, IPX4	124019362112A
USB 3.2 Gen 1, Type C, Receptacle, R/A, Top mount, Center Height 1.5mm, Dual Row SMT, IPX8	124018802112A
USB 3.2 Gen 1, Type C, Receptacle, R/A, Top mount, Center Height 1.5mm, Dual Row SMT, IPX8	124018792112A
USB 3.2 Gen 1, Type C, Receptacle, R/A, Top mount, Center Height 1.5mm, Dual Row SMT, IPX8	124018612112A
USB 3.2 Gen 1, Type C, Receptacle, R/A, Mid mount, Center Height 0.4mm, Dual Row SMT, IPX4	124019032112A
USB 3.2 Gen 1, Type C, Receptacle, R/A, Mid mount, Center Height 0.4mm, Dual Row SMT, IPX8	124018312112A
USB 3.2 Gen 1, Type C, Receptacle, R/A, Mid mount, Center Height 0.4mm, Dual Row SMT, IPX8	124019142112A
USB 2.0, Type C, Receptacle, R/A, Top mount, Center Height 1.5mm, Dual Row SMT, IPX8	124019772112A
USB 2.0, Type C, Receptacle, R/A, Top mount, Center Height 1.5mm, Dual Row SMT, IPX8	124020242112A
USB 2.0, Type C, Receptacle, R/A, Top mount, Center Height 1.5mm, Dual Row SMT, IPX8	12402214E512A
USB 2.0, Type C, Receptacle, R/A, Top mount, Center Height 1.58mm, Dual Row SMT, IPX8	12402050E512A