

ABB430P7W

Industrial Plug

2CMA100336R1000



IEC Plug 30A 3P4W 3phase 480V IP67/69 Clock Position Of
Grounding Contact 7 hour Color code Red, UL/CSA approved
and CE compliant

GENERAL

Product Name	Industrial Plug
Product ID	2CMA100336R1000
Function	Plug
EAN	739269033
Catalog Description	IEC Plug 30A 3P4W 3phase 480V IP67/69, UL/CSA approved and CE compliant
Country of Origin	Czech Republic (CZ)
E-Number Finland	
E-Number Norway	
E-Number Sweden	
Standards	UL 1682, 1686 / CSA C22.2 No. 182.1-13
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	94 millimetre
Product Net Height	94 millimetre
Product Net Length	174 millimetre
Product Net Depth	174 millimetre
Product Net Weight	0.4 kilogram

TECHNICAL

Product Main Type	TP
Color	Red
Number of Poles	4
Clock Position	7Hour
Rated Current	30 ampere
Rated Voltage	480 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67 IP69
Cable Cross-Section	2.5...6 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	Straight
Product Group	Tough&Safe

PACKAGING

Package Width	95 millimetre
Package Height	175 millimetre
Package Gross Weight	0.4 kilogram
Package Length	95 millimetre
Package Units	box 1 piece