

Han 10B Docking Frame IP67 HTE0



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 010 1719
Specification	Han 10B Docking Frame IP67 HTE0
HARTING eCatalogue	https://b2b.harting.com/09300101719

Identification

Category	Accessories
Type of accessory	Docking frame
Description of the accessory	Rear mounting

Version

Size	10 B
Details	Pull-in-range x-axis: ± 1 mm Pull-in-range y-axis: ± 1 mm Pull-in-range z-axis: - 0.5 / +1 mm

Technical characteristics

Mating cycles	≥ 500
Mating cycles with other HMC components	$\geq 10,000$

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (accessories)	Stainless steel

Commercial data

Packaging size	1
Net weight	378.3 g



Pushing Performance
Since 1945

Commercial data

Country of origin	China
European customs tariff number	85389099
ETIM	EC002312
eCl@ss	27440206 Module carrier frame for industrial connectors