

MALLORY**Mallory Sonalert
Products Inc.**

Part #

PK-27H36EPSQ**Sales Outline Drawing**

Revision

A

**May not be suitable for all Medical and Aerospace applications.
Contact Mallory Sonalert to discuss your application.**

Oscillation Frequency (Hz)	3500 \pm 500
Operating Voltage (VDC)	3.0 ~ 24
Rated Voltage (VDC)	12
Current Consumption Max. (mA)	18 at Rated Voltage
Sound Pressure Level Min. (dB)	95 at 100cm at Rated Voltage
Tone / Pulse Rate	Constant
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 757 UL94HB Plastic Resin (Color: Black)
Lead Pin	Tin Plated Brass
Weight (Grams)	9.8
Options	For other options contact factory

Dimensions: (units: mm)