

**MALLORY****Mallory Sonalert  
Products Inc.**

Part #

**PK-31H40PQ****Sales Outline Drawing**

Revision

**A**

**May not be suitable for all Medical and Aerospace applications.  
Contact Mallory Sonalert to discuss your application.**

Oscillation Frequency (Hz)	4000 $\pm$ 300
Operating Voltage (VDC)	3.0 ~ 16
Rated Voltage (VDC)	12
Current Consumption Max. (mA)	25 at Rated Voltage
Sound Pressure Level Min. (dB)	100 at 30cm at Rated Voltage
Tone / Pulse Rate	Constant
Operating Temperature (°C)	-20 ~ +90
Storage Temperature (°C)	-30 ~ +100
Housing	ABS 777D UL94HB Plastic Resin (Color: Black)
Lead Pin	Tin Plated Brass
Weight (Grams)	4.2
Condition by wave soldering (°C)	260 $\pm$ 5 / within 5 sec
Condition by hand soldering (°C)	350 $\pm$ 20 / within 5 sec
Options	For other options contact factory

**Dimensions:** (units: mm)