

**May not be suitable for all Medical and Aerospace applications.
Contact Mallory Sonalert to discuss your application.**

Oscillation Frequency (Hz)	2800 \pm 500
Operating Voltage (VDC)	5 ~ 15
Rated Voltage (VDC)	12
Current Consumption Max. (mA)	200 at Rated Voltage
Sound Pressure Level Min. (dB)	105 at 100cm at Rated Voltage
Tone / Pulse Rate	Fast Pulse 3.0 PPS
LED Type	Yellow
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 757 UL94HB Plastic Resin (Color: Black)
Lead Wires	20 AWG
Weight (Grams)	78
Options	For other options contact factory

Dimensions: (units: mm)

