

**May not be suitable for all Medical and Aerospace applications.
Contact Mallory Sonalert to discuss your application.**

Oscillation Frequency (Hz)	3500 \pm 500
Operating Voltage (VDC)	3.0 ~ 20
Rated Voltage (VDC)	12
Current Consumption Max. (mA)	20 at Rated Voltage
Sound Pressure Level Min. (dB)	100 at 30cm at Rated Voltage
Tone / Pulse Rate	Constant
Operating Temperature (°C)	-20 ~ +90
Storage Temperature (°C)	-30 ~ +100
Housing	ABS 757 UL94HB Plastic Resin (Color: Black)
Lead Wire	28 AWG
Weight (Grams)	7.5
Options	For other options contact factory

Dimensions: (units: mm)

