

MALLORY**Mallory Sonalert
Products Inc.****Part # PF-12N40PEDR-24VICQ****Sales Outline Drawing****Revision A**

**May not be suitable for all Medical and Aerospace applications.
Contact Mallory Sonalert to discuss your application.**

Oscillation Frequency (Hz)	4100 \pm 500
Operating Voltage (VDC)	6 ~ 28
Rated Voltage (VDC)	24
Current Consumption Max. (mA)	200 at Rated Voltage
Sound Pressure Level Min. (dB)	85 at 10cm at Rated Voltage
Tone / Pulse Rate	Fast Pulse 3PPS \pm 20% at Rated Voltage
LED Type	Red
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	PPO plastic resin (Color: Black)
Lead Pin	Tin Plated Brass
Weight (Grams)	1.3
Condition by reflow soldering (°C)	260 \pm 5 / 5 sec
Condition by hand soldering (°C)	350 \pm 20 / within 5 sec
Options	For other options contact factory

Dimensions: (units: mm)