
MALLORY Mallory Sonalert	Part # ASI09N40MQ
<b>Products Inc.</b>	
Sales Outline Drawing	Revision

## May not be suitable for all Medical and Aerospace applications. Contact Mallory Sonalert to discuss your application.

	je de la companya de
Oscillation Frequency (Hz)	$4000 \pm 300$
Operating Voltage (VDC)	2.5 ~ 5.5
Rated Voltage (VDC)	5.0
Current Consumption Max. (mA)	2 at Rated Voltage
Sound Pressure Level Min. (dB)	80 at 10cm at Rated Voltage
Tone / Pulse Rate	Constant
Operating Temperature (°C)	-20 <b>~</b> +100
Storage Temperature (°C)	-30 ~ +110
Housing	LCP (Color: Black)
Type of Connection	SMD
Weight (Grams)	0.8
Condition by reflow soldering (°C)	$250 \pm 5 / 5 \text{ sec}$
Condition by hand soldering (°C)	$350 \pm 20$ / within 5 sec
Options	For other options contact factory

## **Dimensions:** (units: mm)



Attention: Must be installed with correct polarity.

Units come with wash label and are suitable for aqueous wash