

MALLORY**Mallory Sonalert
Products Inc.**

Part #

PS-733EWDYQ**Sales Outline Drawing**

Revision

A

**May not be suitable for all Medical and Aerospace applications.
Contact Mallory Sonalert to discuss your application.**

| | |
|--------------------------------|-----------------------------------|
| Oscillation Frequency (Hz) | 2500 ~ 4500 |
| Operating Voltage (VDC) | 5 ~ 15 |
| Rated Voltage (VDC) | 12 |
| Current Consumption Max. (mA) | 200 at Rated Voltage |
| Sound Pressure Level Min. (dB) | 85 at 300cm at Rated Voltage |
| Tone / Pulse Rate | Siren Sweep |
| LED Type | Yellow |
| Operating Temperature (°C) | -20 ~ +70 |
| Storage Temperature (°C) | -30 ~ +80 |
| Housing | Polycarbonate (Color: Yellow) |
| Lead Wire | 28 AWG |
| Weight (Grams) | 25.2 |
| Options | For other options contact factory |

Dimensions: (units: mm)

