

MALLORY**Mallory Sonalert
Products Inc.**

Part #

PT-2038PQ**Sales Outline Drawing**

Revision

A

**May not be suitable for all Medical and Aerospace applications.
Contact Mallory Sonalert to discuss your application.**

Resonant Frequency (Hz)	3800 \pm 500
Operating Voltage (Vpp)	5 ~ 25
Rated Voltage (Vpp)	5.0
Current Consumption Max. (mA)	5.0 at Rated Voltage
Sound Pressure Level Min. (dB)	85 at 10cm at Rated Voltage
Capacitance (pF)	25,000 \pm 30% at 120 Hz
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 757 Plastic Resin (Color: Black)
Lead Pins	Tin Plated Brass
Weight (Grams)	2
Condition by wave soldering (°C)	260 \pm 5 / within 5 sec
Condition by hand soldering (°C)	350 \pm 20 / within 5 sec
Options	For other options contact factory

Dimensions: (units: mm)

