

# Product data sheet

## Characteristics

# 8940SSD2015

## Well Guard pump panel, Size 2, Motor Logic SSOLR, 240 VAC, NEMA 3R



### Main

Product	Well-Guard Control
Type	Class 8940 type SS
Device application	Pumping

### Complementary

Control Circuit Type	Common control circuit
Control Circuit Voltage	240 V AC 60 Hz 220 V AC 50 Hz
Line Rated Current	45 A
Number of Poles	3
Horsepower Rating	15 hp 240 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO) Push-button START)
Disconnect Type	Fusible disconnect switch
Associated fuse rating	60 A
Fuse type	H or K
Thermal overload type	Motor Logic solid state class 10/20
Protection type	Overload Phase loss Phase unbalance
Device mounting	Surface
Electrical connection	Screw terminal
NEMA size	2
Height	39.06 in (992 mm)
Width	15.16 in (385 mm)
Depth	9.69 in (246 mm)

### Environment

NEMA Rating	NEMA 3R
Enclosure type	Weatherproof enclosure indoor/outdoor
Product certifications	UL listed NEMA

### Ordering and shipping details

Category	21388 - 8940 NSC,NSD
Discount Schedule	CP1
GTIN	00785901011774
Returnability	Yes
Country of origin	MX

## Offer Sustainability

---

REACH Regulation	 REACH Declaration
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration

---

## Contractual warranty

---

Warranty	18 months
----------	-----------

---