



Main

Range	TeSys
Product name	GV2 LE
Product or component type	Mushroom head emergency stop push-button
Device short name	GV2K
Accessory / separate part category	Enclosure accessory

Complementary

Product compatibility	GV2MP LE1GVMEK GV2MC
Type of operator	Latching turn to release
Diameter	1.57 in (40 mm)
Locking options description	Padlock in OFF position
Provided equipment	1 IP55 sealing kit
Height	1.89 in (48 mm)
Width	2.87 in (73 mm)
Net weight	0.26 lb(US) (0.12 kg)
Color	Red

Environment

IP degree of protection	IP55
-------------------------	------

Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	00785901716174
Returnability	Yes
Country of origin	CZ

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------