



Main

Product range	Thorsman TET
Product type	Grommet
Colour	Grey
Quantity per package	Set of 50

Complementary

Material	EPDM
ISO thread	M32
Cable outer diameter	0.55...0.79 in (14...20 mm)
Drilling diameter	1.28 in (32.4 mm)

Environment

IP-Class	IP67
----------	------

Ordering and shipping details

Category	80036 - ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	03606480163821
Returnability	No
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------