

Product data sheet

Specifications



CONTROL STATION 600VAC 5A T-B Ø30 Standard Duty Momentary Pushbuttons 2 N.O

9001BW244

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony 9001BW
Product Or Component Type	Complete control station
Device Short Name	9001BW
Control Station Application	Two functions
Colour Of Base Of Enclosure	Grey

Complementary

Material	Cast aluminium
Cable Entry	1 entry for 1/2" - 14 NPT
Cad Overall Width	2.76 in (70 mm)
Cad Overall Height	4.25 in (108 mm)
Cad Overall Depth	3.58 in (91 mm)
Type Of Operator	momentary
Control Station Composition	1 flush push-button, black, white OPEN 1 flush push-button, black, white CLOSE
Contacts Type And Composition	1 NO + 1 NO
Mechanical Durability	5000000 cycles
[Ie] Rated Operational Current	0.6 A 600 V, AC-1/DC-1 0.75 A 480 V, AC 1.5 A 240 V, AC 3.75 A 120 V, AC
Device Mounting	Surface
Type Of Installation	Indoor/outdoor

Environment

Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Nema Degree Of Protection	NEMA 1 NEMA 4

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60947-1 EN/IEC 60947-5-4 JIS C 4520 EN/IEC 60947-5-5 UL 508
Product Certifications	CSA UL Listed
Environmental Characteristic	Waterproof Dustproof

Ordering and shipping details

Category	US10CS121421
Discount Schedule	0CS1
Gtin	785901857396
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.89 in (22.581 cm)
Package 1 Width	3.50 in (8.89 cm)
Package 1 Length	22.58 in (57.355 cm)
Package 1 Weight	2.50 lb(US) (1.134 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov