XVBC8G6

Harmony XVB, Illuminated unit for modular tower lights, plastic, blue, Ø70, integral "flash" discharge tube, 10 joule, 120 V AC





Main

Range of Product	Harmony XVB Universal
Product or Component Type	Indicator bank
Beacon or indicator bank unit type	Illuminated unit
Signalling type	Flashing
Mounting diameter	2.76 in (70 mm)
Component name	XVBC
Material	Polycarbonate
Light source	Integral flash discharge tube, blue
Bulb type	Flash discharge tube
[Us] rated supply voltage	120 V AC
Flash energy	10 J

Complementary

Assembly style	Customer assembly, up to 5 units
Connections - terminals	Screw clamp terminals, <= 1 x 1.5 mm² with cable end
[Ui] rated insulation voltage	250 V IEC 60947-1
Nominal voltage limit	0.851.1 Un IEC 60947-5-1
Current consumption	< 290 mA AC
[Uimp] rated impulse withstand voltage	4 kV IEC 60947-1
Flashing frequency	1 Hz
CAD overall width	2.76 in (70 mm)
CAD overall height	6.18 in (157 mm)
CAD overall depth	2.76 in (70 mm)
Net Weight	0.69 lb(US) (0.315 kg)

Environment

Product Certifications	UL 508 CCC GOST CSA C22-2 No 14	
Standards	EN/IEC 60947-5-1	
Protective treatment	TC	
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)	
Electrical shock protection class	Class I on support tube IEC 61140 Class II on base unit IEC 61140	
IP degree of protection	IP65 on fixing base XVBZ0. IEC 60529 IP66 on base unit IEC 60529	
NEMA degree of protection	NEMA 4X UL 508 indoor)	

Ordering and shipping details

Category	22611 - XVB-STACKLIGHTS	
Discount Schedule	XV	
GTIN	3389110845815	
Nbr. of units in pkg.	1	
Package weight(Lbs)	11.11 oz (315 g)	
Returnability	No	
Country of origin	CZ	

Packing Units

•	
Unit Type of Package 1	PCE
Package 1 Height	7.36 in (18.7 cm)
Package 1 width	3.15 in (8 cm)
Package 1 Length	3.15 in (8 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	12
Package 2 Weight	9.91 lb(US) (4.493 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product	
California proposition 65	WARNING: This product can expose you to chemicals including: Lead ar lead compounds, which is known to the State of California to cause canc and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	
REACh Regulation	☑ REACh Declaration	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
Mercury free	Yes	
RoHS exemption information	₫Yes	
China RoHS Regulation	☐ China RoHS Declaration	
Environmental Disclosure		
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	

Contractual warranty


- Contraction from the contract of	
Warranty	18 months

XVBC8G6

Indicator Bank with "Flash" Discharge Tube Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



- (1) Base unit XVBC07, to be ordered separately
- (2) Illuminated or audible signalling unit XVBC •••, to be ordered separately
- (3) "Flash" unit

Number of illuminated or audible signalling units other than "flash" tube	b in mm	b in in.
1	295	11.61
2	358	14.09
3	421	16.57
4	484	19.06