



### Main

|                                 |                       |
|---------------------------------|-----------------------|
| Range of product                | Harmony 9001K         |
| Product or component type       | Push-button           |
| Device short name               | K                     |
| Operator additional information | Full guard in plastic |

### Complementary

|                                |                            |
|--------------------------------|----------------------------|
| Bezel material                 | Chromium plated metal      |
| Mounting diameter              | 1.18 in (30 mm)            |
| Light source                   | Without                    |
| Light block supply             | Without supply             |
| Contacts type and composition  | 2 NO + 2 NC                |
| [Ie] rated operational current | 10 A, AC-15<br>10 A, DC-13 |
| Contact operation              | Standard                   |
| Device presentation            | Complete product           |

### Environment

|                           |                                                                            |
|---------------------------|----------------------------------------------------------------------------|
| Product certifications    | NEMA<br>UL listed file E42259 CCN NKCR<br>CE<br>CSA LR 25490 class 3211 03 |
| NEMA degree of protection | NEMA 1/2/3/3R/4/6/12/13                                                    |

### Ordering and shipping details

|                   |                               |
|-------------------|-------------------------------|
| Category          | 21426 - 9001 K (NOT KA,KM,KX) |
| Discount Schedule | CS1                           |
| GTIN              | 00785901398479                |
| Returnability     | Yes                           |
| Country of origin | MX                            |

### Offer Sustainability

|                            |                                                                                                                                                                                      |
|----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                |
| REACH Regulation           |  <a href="#">REACH Declaration</a>                                                                |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes                                                                                                                                                                                  |
| RoHS exemption information |  <a href="#">Yes</a>                                                                              |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>                                                           |
| Environmental Disclosure   |  <a href="#">Product Environmental Profile</a>                                                    |

|                     |                                                                                                                              |
|---------------------|------------------------------------------------------------------------------------------------------------------------------|
| Circularity Profile | No need of specific recycling operations                                                                                     |
| WEEE                | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|