



Main

Range of product	Harmony 9001K
Product or component type	Pilot light
Device short name	K

Complementary

Bezel material	Chromium plated metal
Mounting diameter	1.18 in (30 mm)
Lens type	Fresnel plastic
Cap/operator or lens colour	White
Light block supply	Via transformer 110 V AC 50/60 Hz Via transformer 120 V AC 50/60 Hz
Shape of screw head	Round
Operating mode	Push-to-test

Environment

Product certifications	UL listed file E42259 CCN NKCR CSA LR25490 class 3211 03 CE
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

Ordering and shipping details

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	00785901036029
Returnability	No
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------