

# Product data sheet

Specifications

cord set, Modicon M340, 40-way terminal, 2 x HE10 connector, 3 m



BMXFCC303

Product availability : Stock - Normally stocked in distribution facility

## Main

|                                       |  |
|---------------------------------------|--|
| Range of Product                      | Modicon X80  |
| Accessory / Separate Part Type        | Preformed cordset                                      |
| Accessory / separate part designation | Preformed cordset for Telefast Advantys ABE7 sub-bases |
| Accessory / separate part destination | For I/O module with 40-way connectors                  |
| Number of cables                      | 2  |
| Electrical connection                 | 1 connector 40 ways<br>2 connectors HE10               |
| Cable length                          | 9.84 ft (3 m)  |

## Complementary

|                       |                       |
|-----------------------|-----------------------|
| Total number of wires | 40                    |
| Wire section          | 0.00 in² (0.324 mm²)  |
| Net Weight            | 2.07 lb(US) (0.94 kg) |

## Ordering and shipping details

|                   |                    |
|-------------------|--------------------|
| Category          | 18160-MODICON M340 |
| Discount Schedule | PC34               |
| GTIN              | 3595863919806      |
| Returnability     | Yes                |
| Country of origin | TN                 |

## Packing Units

|                              |                      |
|------------------------------|----------------------|
| Unit Type of Package 1       | PCE                  |
| Number of Units in Package 1 | 1                    |
| Package 1 Height             | 2.17 in (5.500 cm)   |
| Package 1 Width              | 9.65 in (24.500 cm)  |
| Package 1 Length             | 9.65 in (24.500 cm)  |
| Package 1 Weight             | 31.78 oz (901.000 g) |
| Unit Type of Package 2       | S02                  |

|                              |                              |
|------------------------------|------------------------------|
| Number of Units in Package 2 | 6                            |
| Package 2 Height             | 5.91 in (15.000 cm)          |
| Package 2 Width              | 11.81 in (30.000 cm)         |
| Package 2 Length             | 15.75 in (40.000 cm)         |
| Package 2 Weight             | 12.47 lb(US) (5.655 kg)      |
| Unit Type of Package 3       | P12                          |
| Number of Units in Package 3 | 288                          |
| Package 3 Height             | 39.76 in (101.000 cm)        |
| Package 3 Width              | 31.50 in (80.000 cm)         |
| Package 3 Length             | 47.24 in (120.000 cm)        |
| Package 3 Weight             | 6508.05 lb(US) (2952.000 kg) |

### Offer Sustainability

|                            |   |
|----------------------------|---|
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>   |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a>  |
| RoHS exemption information | <a href="#">Yes</a>   |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

### Recommended replacement(s)