

Product data sheet

Specifications



Push button head, Harmony XAC, plastic, black, booted, operating travel 16mm, 25...+ 70 degree C

XACB9212

Product availability : Stock - Normally stocked in distribution facility

Main

Range of Product	Harmony XAC
Product or Component Type	Head for push-button
Component name	XACB
Marking	Unmarked
Operator additional information	Booted
Operating travel	0.63 in (16 mm)
Cap/Operator or lens colour	Black
Product Compatibility	XESD1281 XESD1191 XESD1181 XESD1291
Sale per indivisible quantity	10

Complementary

Net Weight	0.01 lb(US) (0.005 kg)
------------	------------------------

Environment

Standards	EN 60947-5-1 CSA C22.2 No 14 IEC 60947-5-1
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Vibration resistance	15 gn 10...500 Hz)IEC 60068-2-6
Shock resistance	100 gn IEC 60068-2-27
Electrical shock protection class	Class II IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK08 EN 50102

Ordering and shipping details

Category	22473-PUSHBUTTON, PENDANTS
----------	----------------------------

Discount Schedule	CS2
GTIN	3389110640946
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.18 in (3.0 cm)
Package 1 Width	5.51 in (14.0 cm)
Package 1 Length	7.09 in (18.0 cm)
Package 1 Weight	0.21 oz (6.0 g)
Unit Type of Package 2	BAG
Number of Units in Package 2	10
Package 2 Height	7.09 in (18.0 cm)
Package 2 Width	1.18 in (3.0 cm)
Package 2 Length	5.51 in (14.0 cm)
Package 2 Weight	2.43 oz (69.0 g)
Unit Type of Package 3	S02
Number of Units in Package 3	200
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	11.81 in (30.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	3.76 lb(US) (1.706 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)