# **Product data sheet**

Specifications





Indicator bank, Harmony XVB, illuminated unit, plastic, red, 70mm, integral flash discharge tube, 10joule, 24V AC/DC

XVBC8B4

Product availability: Stock - Normally stocked in distribution facility

## Main

Range Of Product	Harmony XVB Universal
Product Or Component Type	Indicator bank
Beacon Or Indicator Bank Unit Type	Illuminated unit
Signalling Type	Flashing
Mounting Diameter	2.76 in (70 mm)
Component Name	XVBC
Material	Polycarbonate
Light Source	Integral flash discharge tube, red
Bulb Type	Flash discharge tube
[Us] Rated Supply Voltage	24 V AC/DC
Flash Energy	10 J

## Complementary

Assembly Style	Customer assembly, up to 5 units
Connections - Terminals	Screw clamp terminals, <= 1 x 1.5 mm² with cable end
[Ui] Rated Insulation Voltage	250 V IEC 60947-1
Nominal Voltage Limit	0.851.1 Un IEC 60947-5-1
Current Consumption	< 1300 mA AC < 850 mA DC
[Uimp] Rated Impulse Withstand Voltage	4 kV IEC 60947-1
Flashing Frequency	1 Hz
Cad Overall Width	2.76 in (70 mm)
Cad Overall Height	6.18 in (157 mm)
Cad Overall Depth	2.76 in (70 mm)
Net Weight	0.67 lb(US) (0.305 kg)

## **Environment**

Product Certifications	CCC
	EAC
	CSA C22-2 No 14
	UL 508

Apr 3, 2024 Life Is On Schneider

Standards	IEC 60947-5-1
Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Electrical Shock Protection Class	Class I on support tube IEC 61140 Class II on base unit IEC 61140
Ip Degree Of Protection	IP65 on fixing base XVBZ0. IEC 60529 IP66 on base unit IEC 60529
Nema Degree Of Protection	Type 4X UL indoor)

## Ordering and shipping details

Category	US100XV22611
Discount Schedule	00XV
Gtin	3389110845679
Returnability	Yes
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.15 in (8.0 cm)
Package 1 Width	3.15 in (8.0 cm)
Package 1 Length	7.48 in (19.0 cm)
Package 1 Weight	11.29 oz (320.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	9.50 lb(US) (4.307 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


## XVBC8B4

#### **Dimensions Drawings**

## Indicator Bank with "Flash" Discharge Tube Unit

#### **Dimensions**

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get  $\mathbf{b}$  dimension.



- (1) Base unit XVBC07, to be ordered separately
- (2) Illuminated or audible signalling unit XVBC•••, to be ordered separately
- (3) "Flash" unit

Number of illuminated or audible signalling units other than "flash" tube	b in mm	b in in.
1	295	11.61
2	358	14.09
3	421	16.57
4	484	19.06