

Product data sheet

Specifications

SQUARE D

Green Premium™



Industrial control transformer, Type T, 1 phase, 3000VA, 600V primary, 120/240V secondary, 50/60Hz

9070T3000D37

Product availability : Stock - Normally stocked in distribution facility

Main

Product Type	Industrial Control Transformer
Power Rating	3000 VA
Type	T

Complementary

Number of Phases	1 phase 3000 VA UL 3000 VA CSA 3000 VA NOM 2000 VA
Temperature Rise	115 °C
Electrical Connection	Screw clamp terminals
Height	8.75 in (222.25 mm)
Width	9 in (228.60 mm)
Depth	7.24 in (183.90 mm)
Fingersafe Cover Compatibility	FSC2

Environment

Certifications	UL Listed CSA
Enclosure Type	Not rated (open device)
Insulation Temperature	356 °F (180 °C)

Ordering and shipping details

Category	16205-9070 T (NOT TF) 3000 - 5000VA
Discount Schedule	CP8
GTIN	785901849605
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.60 in (32.004 cm)
Package 1 Width	12.00 in (30.48 cm)
Package 1 Length	14.80 in (37.592 cm)
Package 1 Weight	59.90 lb(US) (27.17 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	10 Years
----------	----------

Recommended replacement(s)