Product data sheet

Specifications







CONTROL STATION + OPERATORS

9001KYK26

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| Range Of Product | Harmony 9001KY | |
|------------------------------|---|--|
| Product Or Component Type | Control station | |
| Device Short Name | 9001KY | |
| Provided Equipment | Label plate OPEN-CLOSE | |
| Contact Block Name | KA1 | |
| Product Specific Application | For hoisting and mechanical handling applications | |
| Level Or Class | Class III Class II Division 2 Group G | |

Complementary

| Enclosure/Cubicle Description | Wall-mounted enclosure 2 cut-outs Ø 30 mm |
|-----------------------------------|---|
| Enclosure Material | Die cast zinc alloy Gray |
| Type Of Installation | Indoor/outdoor |
| Control Station Composition | 2 push-buttons 2 NO + 2 NC |
| Mechanical Interlocking | Without mechanical interlock |
| Connector Type | Screw clamp connector |
| Connections - Terminals | Direct connection AWG 2) solid stranded Direct connection AWG 12) solid stranded Direct connection AWG 24) solid stranded |
| [Ue] Rated Operational Voltage | 300 V |
| [le] Rated Operational Current Ac | 10 A |

Environment

| Nema Degree Of Protection | NEMA 4 NEMA 3 NEMA 1 NEMA 13 | |
|--|--|--|
| Environmental Characteristic | Resistant against immersion in water Dust and oil resistant | |
| Product Certifications | UL Listed | |
| Ambient Air Temperature For Operation | -13140 °F (-2560 °C) | |
| Ambient Air Temperature For Storage | -40158 °F (-4070 °C) | |

Ordering and shipping details

Category

US10CS121426

| Discount Schedule | 0CS1 |
|-------------------|--------------|
| Gtin | 785901039990 |
| Returnability | No |
| Country Of Origin | МХ |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 13.97 in (35.484 cm) |
| Package 1 Width | 5.50 in (13.97 cm) |
| Package 1 Length | 35.48 in (90.129 cm) |
| Package 1 Weight | 4.00 lb(US) (1.814 kg) |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |