



Main

Product or component type	Dry Sealed Transformer
Full Capacity Taps	2 5 % FCBN

Complementary

Enclosure Code	54X
Phase	3 phase
Primary to Secondary Voltage	480 V delta 208Y/120 V
Power Rating	15 kVA
Temperature rise	115 °C
Height	23 in (584.20 mm)
Width	647.70 mm (25.5 in)
Depth	349.25 mm (13.75 in)
Enclosure mounting	Floor
Enclosure material	Stainless steel

Environment

Enclosure Type	NEMA 4X
Insulation temperature	356 °F (180 °C)
Product certifications	UL listed CULus CSA

Ordering and shipping details

Category	16277 - RESIN LVGP XFMR
Discount Schedule	PE2
Returnability	No
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Contractual warranty	
Warranty	18 months