



Main

Product	Reversing Drum Switch
Enclosure Rating	NEMA 4
Horsepower	1.5 Hp 115 V AC, 1 phase 3 Hp 230 V AC, 1 phase 5 Hp 460 V AC, 1 phase 5 Hp 575 V AC, 1 phase 5 Hp 200 V AC, 3 phase 5 Hp 230 V AC, 3 phase 7.5 Hp 460 V AC, 3 phase 7.5 Hp 575 V AC, 3 phase 2 Hp 115 V DC 2 hp 230 V DC
Maximum Rated Voltage	600 V AC 250 V DC
Number of Poles	3P


Complementary

Certifications	CSA UL listed
Electrical Connection	Screw-clamp terminals
Type	B

Ordering and shipping details

Category	21116 - 2601
Discount Schedule	CP1
GTIN	00785901784449
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------