



## Main

Range	Thalassa
Product name	Thalassa TBP
Device application	Multi-purpose
Category	Industrial box
Height	4.57 in (116 mm)
Width	4.57 in (116 mm)
Depth	2.44 in (62 mm)
Internal height	4.13 in (105 mm)
Internal width	4.13 in (105 mm)
Internal depth	2.17 in (55 mm)
Enclosure mounting	Wall mounted
Device composition	1 body 1 cover 4 cover screw
Quantity per set	Set of 5
Body type	One piece moulded
Type of front cover	Low plain cover
Cover fixing	Plastic screws
Lock type	Captive screw flat outside sealed area
Removable parts	Cover by captive screws

## Complementary

Material	polycarbonate
Color	Grey RAL 7035)
Standards	IEC 62208 UL 508 A
Product certifications	UL DEMKO SEMKO TÜV
Electrical insulation class	Class II
IP degree of protection	IP66 NEMA 4.4X
IK degree of protection	IK08 IEC 62262
Fire resistance	1760 °F (960 °C)
Ambient air temperature for storage	5...140 °F (-15...60 °C)
Operating temperature	-13...176 °F (-25...80 °C)
Net weight	0.38 lb(US) (0.171 kg)

## Ordering and shipping details

Category	80033 - ENCLOSURE SYSTEMS POLYESTER
Discount Schedule	ES1
GTIN	00785901855088
Returnability	No
Country of origin	HU

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------