

Product data sheet

Specifications



CANopen standard cable - IP20 - UL - IEC 60332-2 - 50 m

TSXCANCB50

Product availability : Stock - Normally stocked in distribution facility

Main

Range of Product	CANopen
Bus type	CANopen
Accessory / separate part category	Connection accessories
Accessory / Separate Part Type	Connecting cable
Accessory / separate part destination	CANopen bus
Cable length	164.04 ft (50 m)

Complementary

Marking	CE
Net Weight	7.89 lb(US) (3.58 kg)

Environment

Product Certifications	UL
IP Degree of Protection	IP20

Ordering and shipping details

Category	22558-TSX PREMIUM, ATRIUM & PL7 PRO
Discount Schedule	PC22
GTIN	3595862011921
Returnability	No
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.27 in (21 cm)
Package 1 Width	13.78 in (35 cm)
Package 1 Length	13.78 in (35 cm)
Package 1 Weight	10.67 lb(US) (4.838 kg)

Unit Type of Package 2	P12
Number of Units in Package 2	24
Package 2 Height	40.94 in (104 cm)
Package 2 Width	31.50 in (80 cm)
Package 2 Length	47.24 in (120 cm)
Package 2 Weight	282.43 lb(US) (128.11 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)