



Main

Range of product	Altivar
Product or component type	Braking resistor ATV61 Braking resistor ATV71
Range compatibility	Altivar 312 Altivar 71 Lexium 32i Lexium 52 Lexium 32 Altivar 61
Product compatibility	LXM32MC10N4 LXM32MD85N4 ATV312HD11M3 ATV312HD15M3 ATV61HD11M3X ATV61HD37N4 ATV61HD55Y ATV61HD75Y ATV61WD45N4 ATV61WD45N4C ATV71HD11M3X ATV71HD37N4 ATV71HD45Y ATV71HD55Y ATV71WD37N4
Continuous power	1000 W
Average power available	1 KW 122 °F (50 °C) 1.15 kW 104 °F (40 °C)
Ohmic value	10 Ohm

Complementary

Electrical connection	M6 bar wire drive Terminal <= 2.5 mm ² / AWG 14 temperature control switch
Protection type	Thermal protection via drive or temperature control switch 120 °C
[Ue] rated operational voltage	24 V DC 0.1 A 250 V AC 1 A
Temperature controlled switch contact resistance	60 µOhm
Net weight	24.25 lb(US) (11 kg)

Environment

Ambient air temperature for operation	32...122 °F (0...50 °C)
Ambient air temperature for storage	-13...158 °F (-25...70 °C)
IP degree of protection	IP20

Ordering and shipping details

Category	22154 - ATV320/ATV312/ATV32 ACCESSORIES
Discount Schedule	CP4B
GTIN	00785901684923
Returnability	No
Country of origin	DE

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------

Braking Resistor

Dimensions

