

Product data sheet

Specifications



Modicon STB - mounting base - for I/O module - 13.9 mm

STBXBA1000

Product availability : Stock - Normally stocked in distribution facility

Main

Range of Product	Modicon STB distributed I/O solution
Accessory / separate part category	Mounting accessories
Accessory / Separate Part Type	Base
Accessory / separate part designation	Mounting base
Accessory / separate part destination	I/O module

Complementary

Product Compatibility	STBDDO3605 STBDDI3230 STBDDI3420 STBDDO3415 STBDDI3610 STBDDO3230 STBACI1225 STBDDI3425 STBDDI3615 STBDDO3410 STBART0200 STBDDO3200 STBDDO3600 STBAVI1275 STBAVO1265 STBAVO1250 STBACI1230 STBAVI1255 STBACO1225 STBAVO1255 STBACO1210 STBAVI1270
Width	0.55 in (13.9 mm)
Net Weight	0.05 lb(US) (0.024 kg)

Ordering and shipping details

Category	18215-ADVANTYS STB I/O
Discount Schedule	PC32
GTIN	3595862061988
Returnability	No
Country of origin	IN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.79 in (2.0 cm)
Package 1 Width	1.97 in (5.0 cm)
Package 1 Length	5.12 in (13.0 cm)
Package 1 Weight	1.23 oz (35.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	96
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	7.41 lb(US) (3.36 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)