

Product data sheet

Specifications



CANopen SUB-D9 female connector - bended at 90° w additional SUB-D9 - IP20

TSXCANKCDF90TP

Product availability : Stock - Normally stocked in distribution facility

Main

Range of Product	CANopen
Bus type	CANopen
Accessory / separate part category	Connection accessories
Accessory / Separate Part Type	Connector with line terminator
IP Degree of Protection	IP20
Accessory / separate part destination	CANopen bus

Complementary

Electrical connection	1 female connector SUB-D 9 elbowed 1 male connector SUB-D 9
Net Weight	0.11 lb(US) (0.051 kg)

Ordering and shipping details

Category	22558-TSX PREMIUM, ATRIUM & PL7 PRO
Discount Schedule	PC22
GTIN	3595862030687
Returnability	No
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.63 in (1.600 cm)
Package 1 Width	4.13 in (10.500 cm)
Package 1 Length	5.87 in (14.900 cm)
Package 1 Weight	1.80 oz (51.000 g)
Unit Type of Package 2	S04
Number of Units in Package 2	200
Package 2 Height	11.81 in (30.000 cm)

Package 2 Width	15.75 in (40.000 cm)
Package 2 Length	23.62 in (60.000 cm)
Package 2 Weight	24.58 lb(US) (11.150 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)