

Product data sheet

Specifications



CANopen standard cable - IP20 - IEC 60332-1 - 50 m

TSXCANCA50

Product availability : Stock - Normally stocked in distribution facility

Main

Range of Product	CANopen
Bus type	CANopen
Accessory / separate part category	Connection accessories
Accessory / Separate Part Type	Connecting cable
Accessory / separate part destination	CANopen bus
Cable length	164.04 ft (50 m)

Complementary

Marking	CE
Net Weight	10.87 lb(US) (4.93 kg)

Environment

IP Degree of Protection	IP20
-------------------------	------

Ordering and shipping details

Category	22531-PLCS, TWIDO, TWD
Discount Schedule	PC12
GTIN	3595863859485
Returnability	No
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.46 in (21.500 cm)
Package 1 Width	13.39 in (34.000 cm)
Package 1 Length	13.39 in (34.000 cm)
Package 1 Weight	11.24 lb(US) (5.100 kg)
Unit Type of Package 2	P12

Number of Units in Package 2	18
Package 2 Height	31.50 in (80.000 cm)
Package 2 Width	31.50 in (80.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	211.64 lb(US) (96.000 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)