

Product data sheet

Characteristics

LT6CT4001

current transformer TeSys T LT6CT - 400/1 A -
accuracy: class 5P



Main

Range	TeSys
Device short name	LT6CT
Product or component type	Current transformer
Range compatibility	TeSys T motor controller

Complementary

Current transformer ratio	400/1
Accuracy class	Class 5P
Precision limit factor	15
[Ui] rated insulation voltage	690 V
Diameter	0.39 in (10 mm)
Cable cross section	0.47 in ² (300 mm ²)
Height	4.21 in (107 mm)
Width	3.74 in (95 mm)
Depth	0.98 in (25 mm)
Net weight	1.21 lb(US) (0.55 kg)

Environment

Standards	BS 7626 IEC 60185
Maximum ambient air temperature for operation	122 °F (50 °C)

Ordering and shipping details

Category	22338 - SOLID STATE OVERLOAD RELAYS
Discount Schedule	I12
GTIN	00785901830511
Returnability	No
Country of origin	GB

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Contractual warranty	
Warranty	18 months