





# Light block, Harmony 9001K, Harmony 9001SK, shallow depth, 30mm, LED green, 110-120V

9001KM58LG

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

Range Of Product	Harmony 9001K Harmony 9001SK
Product Or Component Type	Light block
Device Short Name	9001K
Bulb Base	BA 9s
Light Block Supply	Direct

# Complementary

Net Weight	0.25 lb(US) (0.115 kg)
Light Source	LED
Light Block Colour	Green
[Us] Rated Supply Voltage	110120 V AC/DC
[Us] Rated Supply Voltage	110120 V
Light Block Supply	Full voltage
Light Source Colour	Green
Dimension Type	Shallow depth
Size	30 mm

## **Environment**

Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ip Degree Of Protection	IP20 IEC 60529
Standards	CSA C22.2 No 14 EN/IEC 60947-1 JIS C 852 JIS C 4520 UL 508 EN/IEC 60947-5-4 EN/IEC 60947-5-1
Product Certifications	UL 508 NEMA
Electrical Shock Protection Class	Class II IEC 61140
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6

Life Is On Schneider Apr 5, 2024

# Ordering and shipping details

Category	US10CS121435
Discount Schedule	0CS1
Gtin	785901637332
Returnability	No
Country Of Origin	MX

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.80 in (4.572 cm)
Package 1 Width	2.10 in (5.334 cm)
Package 1 Length	3.60 in (9.144 cm)
Package 1 Weight	4.00 oz (113.398 g)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information


Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

## **Dimensions Drawings**

#### **Dimensions**



e panel thickness: 1 to 6 mm / 0.04 to 0.24 in.