Product data sheet

Specifications





Illuminated push button, Harmony 9001K, metal, plastic guard flush, green, 30mm, spring return, 110...120V, 1 CO

9001K1L1GH13

Product availability: Stock - Normally stocked in distribution facility

Main

| Range Of Product | Harmony 9001K |
|---------------------------------|-------------------------|
| Product Or Component Type | Illuminated push-button |
| Device Short Name | К |
| Type Of Operator | spring return |
| Operator Profile | Green flush |
| Operator Additional Information | Plastic quard |

Complementary

| • | |
|--------------------------------|----------------------------|
| Bezel Material | Metal |
| Mounting Diameter | 1.18 in (30 mm) |
| Light Source | incandescent |
| Light Source | Incandescent bulb |
| Bulb Base | BA 9s |
| Light Block Supply | Via integral transformer |
| [Us] Rated Supply Voltage | 110120 V AC |
| Contacts Type And Composition | 1 C/O |
| Connections - Terminals | Screw clamp terminals |
| Operating Position | Any position |
| [le] Rated Operational Current | 10 A, AC-15 10 A, DC-13 |
| Contact Operation | Standard |
| Device Presentation | Complete product |
| Cap/Operator Or Lens Colour | Green |
| [Us] Rated Supply Voltage | 110120 V |
| Light Block Supply | Via integral transformer |
| Operator Profile | Flush |
| Type Of Operator | Spring return |
| Supply Frequency | 5060 Hz |
| Size | 30 mm |

Environment

| Product Certifications | CSA LR 25490 class 3211 03 NEMA CE UL listed file E42259 CCN NKCR |
|---------------------------|---|
| Nema Degree Of Protection | NEMA 1/2/3/3R/4/6/12/13 |

Ordering and shipping details

| Category | US10CS121426 |
|-------------------|--------------|
| Discount Schedule | 0CS1 |
| Gtin | 785901848790 |
| Returnability | Yes |
| Country Of Origin | US |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|--------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2.40 in (6.096 cm) |
| Package 1 Width | 4.50 in (11.43 cm) |
| Package 1 Length | 2.00 in (5.08 cm) |
| Package 1 Weight | 9.44 oz (267.62 g) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |