

# Product data sheet

Specifications



## Standard motor mechanism module MT250, ComPacT NSX250, 380/415VAC 50/60Hz, 440/480VAC 60Hz

LV431542

Product availability : Stock - Normally stocked in distribution facility

### Main

Device short name	MT250
Product or Component Type	Motor mechanism
Device Application	Automatic spring charging
Range compatibility	ComPacT new generation (ComPacT NSX250 new generation) ComPact (ComPact NSX250) ComPacT new generation (ComPacT NSX DC new generation) NSX250 DC ComPact Compact NSX250 DC PowerPact Multistandard (PowerPact Multistandard) EasyPact (EasyPact CVS250) PowerPact (PowerPact J) PowerPact (PowerPact H)
Control Type	Standard
[Uc] control circuit voltage	380...415 V AC 50/60 Hz 440...480 V AC 60 Hz
Circuit breaker mounting mode	Fixed
Circuit breaker frame rated current	250 A

### Complementary

Control signal type	Maintained Impulse
Circuit breaker response time	< 700 ms open < 80 ms closed
Maximum operating frequency	4 per minute
Maximum power consumption in VA	500 VA closing 500 VA opening
Provided Equipment	SDE adaptor
Locking options description	1 to 3 padlocks Ø 5 to Ø 8 Padlocking in OFF position

### Ordering and shipping details

Category	01081-INTRA-COMPANY COMPONENTS
Discount Schedule	NET
GTIN	3606480020094

Returnability	No
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.76 in (12.1 cm)
Package 1 Width	4.13 in (10.5 cm)
Package 1 Length	6.81 in (17.3 cm)
Package 1 Weight	3.07 lb(US) (1.394 kg)
Unit Type of Package 2	S04
Number of Units in Package 2	15
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	15.75 in (40.0 cm)
Package 2 Length	23.62 in (60.0 cm)
Package 2 Weight	47.46 lb(US) (21.526 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)