

# Product data sheet

Specifications



## FULL-VOLTAGE NON-REVERSING IEC STARTER UNFUSED TYPE 1

LE1D323A62OG70

Product availability : Stock - Normally stocked in distribution facility

### Main

Product or Component Type	Full voltage starter
Range of Product	Instakits
Starter Type	Non reversing

### Complementary

Control Circuit Voltage	120 V AC 50/60 Hz
Current Rating	32 A
Horsepower Rating	2 hp 120 V AC, 1 phase 5 hp 240 V AC, 1 phase 10 hp 208 V AC, 3 phase 10 hp 230 V AC, 3 phase 20 hp 460 V AC, 3 phase 25 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Auxiliary Contacts	1 NO + 1 NC
Protection Type	Switch-disconnector fuse
Location of connection	Line

### Environment

Product Certifications	UL CSA IEC
Enclosure Type	NEMA 1 steel

### Ordering and shipping details

Category	22313-CTRS,D-LINE,ENCL (METAL)
Discount Schedule	I11
GTIN	785901796251
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
Package 1 Height	9.49 in (24.1 cm)
Package 1 Width	10.71 in (27.2 cm)
Package 1 Length	14.49 in (36.8 cm)
Package 1 Weight	10.25 lb(US) (4.65 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)