

NEBO[®]

GRILLA LIGHT™ 300

LIGHT MODES

- High (300 lumens): 6 hours / 20 meters
- Low (100 lumens): 16 hours / 10 meters

DESIGN

- ChromaView™ Technology
- >80 CRI rating (Color Rendering Index)
- Smart Power Control™ (SPC)
- Universal clamp with 180° tilt
- Fits most grills
- Detachable design
- Integrated bottle opener
- Heat-resistant silicone grip
- Anodized aircraft-grade aluminum
- Water and impact-resistant
- Powerful magnetic base

OPERATION

- Top-positioned button

BATTERIES

- Powered by 3 AA batteries (included)

SPECS

- 0.73 lb.
- Light only: (L) 6.5625" x (W) 1" x (D) 1.5"
- Light with clamp: (L) 9.8125" x (W) 3.75" x (D) 1.5"

US PATENTS

- 11,076,460 & 11,516,897



⚠ WARNING CALIFORNIA REQUIRED | Cancer and Reproductive Harm | www.P65Warnings.ca.gov



300 LUMEN GRILL LIGHT WITH CHROMAVIEW™ TECHNOLOGY

The GRILLA Light uses **ChromaView™ Technology** to display true and accurate color clarity with a **high CRI rating (>80)**, so that your food will look as good as it will taste. This detachable **300 lumen work light** features a **powerful magnetic base** and a **universal clamp** designed to fit most grills.

UPC CODE	ITEM	COST	MSRP
645397942801	NEB-ARE-0009		

Natralock Dimensions
(H) 13.58" x (W) 7" x (D) 1.75"
PDQ Dimensions
(H) 2" x (W) 8.42" x (D) 11.1"

