



## Panduct® C3LG6 Flush Duct Cover

### C3LG6

The C3LG6 PVC Flush Wiring Duct Cover features a non-slip, liner to prevent cover slide. Designed with the user in mind, the cover is easy to install and remove. The general-purpose lead-free PVC material is suitable for use in indoor applications. UL 94 flame class of V-0 with a UL recognized continuous-use temperature up to 122°F (50°C). 0.37" x 3.25" (9.4 mm x 82.6 mm) and 6' (1.83 m) long. Color Light Gray.

### Specifications

Application	Cover for Wiring Duct
Note	Base and Cover Sold Separately.
Product Type	Flushed Duct Cover
Sub Brand	Panduct®
Color	Light Gray
For Use With	Type G, Type F, Type D and Type FS Duct Base
Material	PVC
Material Properties	Lead-Free
Standards Met	UL Recognized; Flammability Ratings: UL94 V-0; CSA Certified; CE Compliant; RoHS Compliant
Compatible Duct Width (In.)	3
Compatible Duct Width (mm)	76.2
Overall Height (In.)	0.37
Overall Height (mm)	9.4
Overall Length (ft.)	6
Overall Length (m)	1.8
Overall Width (In.)	3.25
Overall Width (mm)	82.6
Mount Method	Snap-On
Wiring Duct Style	Flush Cover
Part Features	Cover with non-slip liner to prevent cover slide, flush cover design. Designed for easy install and removal. PVC Lead-free material

**Packaging Detail**

UPC	07498323120
Std. Pkg. Qty.	6
Std. Pkg. Volume (cf)	0.0399
Std. Ctn. Qty.	120
Std. Ctn. Volume (cf)	0.7985