

Product information

77 82 130

Electronics Diagonal Cutter

DIN ISO 9654



- Round head, with small bevel
- Cutting edge hardness approx. 62 HRC
- Durable, load-optimised design with backlash-free box joint
- High, slim sleeves for fine and comfortable gripping between thumb and index finger
- Low-friction double spring for gentle and even opening
- Mirror-polishing instead of chrome-plating to avoid interference in the circuit with flaking chrome parts
- For fine cutting and assembly work, e.g. in electronics and fine mechanics
- Cutters additionally laser hardened, cutter hardness at least 62 HRC



General

Article No.	77 82 130
EAN	4003773089162
Head	mirror polished
Handles	with multi-component grips
Weight	81 g
Dimensions	130 x 81 x 16 mm
Standard	DIN ISO 9654
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities medium hard wire (diameter)	Ø 1.3 mm
Cutting capacities soft wire (diameter)	Ø 0.3 – 1.6 mm
Jaw length (B)	16.2 mm
Jaw thickness (joint) (D)	8.5 mm
Head width (A)	13 mm
Cutting edge length mm (C)	16.2 mm

technical change and errors excepted

