

IKS 20 PZD Screwdriver bit socket

for cruciform head screws POZIDRIV

Description as No. IS 20.

Bits as per DIN ISO 8764-1 PZ.

Code	No.	L	
6187130	IKS 20 PZD 1	28	10
6187210	IKS 20 PZD 2	28	15
6187480	IKS 20 PZD 3	28	15
6187560	IKS 20 PZD 4	28	20



IN 20 Screwdriver bit socket

for hexagon head screws

Screwdriver bit socket, hand-operated, with square drive as per DIN 3120 - C 6.3, ISO 1174 with ball retaining groove. Chrome-plated, knurled grip. Bit in GEDORE vanadium special steel, gun-metal finish.

* not standardised

Code	No.	mm	L	d	t	
6176010	IN 20 3	3	28	12	5,5	20
6176280	IN 20 4	4	28	12	7,0	20
6176360	IN 20 5	5	28	12	8,0	20
6178490	IN 20 6	6	28	12	8,5	25
6178570	IN 20 8*	8	28	12	10,0	25



DIN 7422

2093 HR Hand ratchet

without handle, push-through square 1/4"

Helps you to work quickly in limited spaces where other ratchets or tools do not fit. Especially suitable for the work in confined places like modern car engines in connection with extension 2090-12.

Size Ø 27 x 20 mm.

Code	No.	Description	
6069870	2093 HR-94	Hand ratchet 1/4"	28



2093 Ratchets

1/4" square drive

For hand-operated sockets and accessories with square drive as per DIN 3120 - C 6.3, ISO 1174 ball locking device. GEDORE vanadium steel 31CrV3, mat. No. 1.2208, chrome-plated.

2093 Z-94 9° Ratchet with square coupler, medium toothed, very robust.

2093 U-3 5° Reversible ratchet with dial change, fine toothed.

2093 U-10 15° Reversible ratchet with lever change, locks in middle position, oval head.

Code	No.	Description	L mm	H mm	
6170750	2093 Z-94	Ratchet handle with coupler 1/4"	127	12,0	65
6170590	2093 U-3	Reversible ratchet 1/4"	127	24,0	65
6180470	2093 U-10	Reversible ratchet 1/4"	127	22,2	105



DIN 3122, ISO 3315

2030-2098 Accessories

1/4" square drive

For hand-operated sockets with square drive as per DIN 3120, ISO 1174 with ball locking device. GEDORE vanadium steel 31CrV3, mat. No. 1.2208, chrome-plated, polished.

Code	No.	Description	L mm	
6170080	2030	Convertor 1/4" to 3/8"	26	15
6170160	2087	Tommy bar with sliding "T"	115	40
6170240	2088	Flexible Extension 1/4"	120	45
6170320	2090-2	Extension 1/4"	55	25
6170400	2090-4	Extension 1/4"	97	45
6171210	2090-6	Extension 1/4"	148	50
6173340	2090-12	Extension 1/4"	305	120
6121030	2090 KR 6	Universal extension 1/4"	148	60
6170830	2094	Coupler 1/4"	20	5
6170910	2095	Universal joint 1/4"	38	20
6171050	2097	Swivel handle 1/4"	150	75
6171480	2098	Driving handle 1/4"	140	70



DIN 3122, ISO 3315 - DIN 3123, ISO 3316