

Protective cable conduit system SILVYN® RILL

Holder for SILVYN® RILL



SILVYN® KLICK-S

Conduit holder

Quick and easy to assemble conduit holder for high-quality conduits SILVYN® RILL, impact-resistant polyamid. An open conduit mounting with rib clamping for strain relief and attachment by means of holes for screws. The SILVYN KLICK-S can be used either as a

mounting holder, an end mounting, or as an intermediate support.

Note: For RAL 9005 black, replace last figure of the art.-no. by "5".



SILVYN® KLICK-D

Cover

The SILVYN® KLICK-D cover converts the SILVYN® KLICK-S into a closed conduit holder.

Note: For RAL 9005 black, replace last figure of the art.-no. by "5".



SILVYN® KLICK-V

Connection bracket

The connection bracket for SILVYN® KLICK-S, to link several SILVYN® KLICK-S, suitable for all sizes.

Note: For RAL 9005 black, replace last figure of the art.-no. by "5".



Technical Data	Material:	Standard colour:	Temperature range:
SILVYN® KLICK-S	PA	grey black UV-resistant	-30 °C to +80 °C
SILVYN® KLICK-D	PA	grey black UV-resistant	-30 °C to +80 °C
SILVYN® KLICK-V	PA	grey black UV-resistant	-30 °C to +80 °C

Part number	Designation / PG size	PU pieces
SILVYN® KLICK-S grey		
6181 1110	7	100
6181 1120	9	100
6181 1130	11	50
6181 1190	13,5	50
6181 1140	16	50
6181 1150	21	50
6181 1160	29	30
6181 1170	36	20
6181 1180	48	20
SILVYN® KLICK-D grey		
6181 1200	11	100
6181 1260	13,5	50
6181 1210	16	50
6181 1220	21	50
6181 1230	29	30
6181 1240	36	20
6181 1250	48	20
SILVYN® KLICK-V grey		
6181 1270	-	100