

Soldering Station Kit

Soldering station with free solder wire & tip cleaner

1296771 + 5090726 + 1467280

1296771 – Soldering Station (UK)



Colour	Blue
External Depth	165 mm
Height	87 mm
Max Temperature	450 °C
Min Temperature	150 °C
Power Consumption	48 W
Voltage, Output	24 V ac
Voltage, Supply AC	230 V ac
Width, External	195 mm

5090726 – Lead Free Solder Wire



Flux Type	505, Rosin based Lead Free, 99.3% Tin, 0.7% Copper
Material Composition	Alloy
Max Bit Temperature	370 °C
Melting Temperature	227 °C
Min Bit Temperature	350 °C
Weight	0.5 kg
Wire Diameter	0.7 mm

1467280 – Soldering Tip Cleaner



- Contents made of low abrasive brass shavings
- No water or messy wet sponges necessary
- No temperature drop as in conventional sponges
- Anti-slip pad on the base and an integral adjustable soldering iron rest
- Two concave indents on the top rim
- Dimensions (Dia. x H): ø82x30mm