


# SANYO Cadnica




## Cell Type CP-2400SCR Specifications


Nominal Capacity		2400mAh	
Nominal Voltage		1.2V	
Charging Current	Standard	240mA	
	Fast	3600mA	
Charging Time	Standard	14 to 16Hrs.	
	Fast	about 1Hr.	
Ambient Temperature	Charge	Standard	0°C to +45°C [+32°F to 113°F]
		Fast	5°C to +40°C [+41°F to 104°F]
	Discharge	-20°C to +60°C [-4°F to 140°F]	
Storage		-30°C to +50°C [-22°F to 122°F]	
Internal Impedance (Av.) (at 50% discharge)		4.5mΩ (at 1000Hz)	
Weight		60g/2.11oz	
Dimensions(D)x(H) (with tube)		22.9 <sup>0</sup> <sub>-1</sub> × 43.5 <sup>0</sup> <sub>-1.2</sub> mm 0.90 <sup>0</sup> <sub>-0.04</sub> × 1.71 <sup>0</sup> <sub>-0.05</sub> inch	

### Typical Characteristics


#### Charge




#### Discharge (at high rate)




#### Cell capacity (at various discharge rate)



#### Discharge (at high rate)



#### Discharge (at low rate)



#### Temperature (Charge & Discharge)

