

Ignitors for HI-lamps



Type: **IGNITOR Z 150**
Item number: **140376**

For high pressure sodium lamps (HS),
metal halide lamps (HI) and HI lamps
with ceramic discharge tube (C-HI)

Phasing of the ignition voltage:

60-90 °el and 240-270 °el

Load capacity: 20-100pF

For luminaires of protection class I

120g

Nominal rating [V]: 220-240

Frequency [Hz]: 50-60

Max.Current [A]: 2,0

Ignition voltage [kV]: 4,0-5,0

HS-Lamps [W]: 70(DE)-
150

HI-Lamps [W]: 35-150

Internal loss [W]: 1,50

Inherent heating [K]: 15,00

Max. casing temperature
[°C]: 105

Casing material: Aluminium

Casing LxWxH: 74XØ35

Terminals[mm²]: 0,75-2,5

prepared for protection
class: 1

prepared for degree of
protection: IP20

Unit: 40 pcs.

