PSN02-2301 deTem

SAFETY MULTIBEAM SENSORS



PSN02-2301 | deTem

SAFETY MULTIBEAM SENSORS

Ordering information

deTem4 A/P

Scanning range	Number of beams	Beam sep- aration	System part	Туре	Part no.
3.2 m	4	300 mm	Passive unit	PSN02-2301	1102144

Other models and accessories -> www.sick.com/deTem

Detailed technical data

Features	
Application	Normal industrial environment
Functional principle	Active/passive
System part	Passive unit
Type of diversion	Fibre-optic deflection
Scanning range category	Low scanning range
Scanning range	3.2 m
Dimension of the light path	
Typical	0.5 m 3.2 m
Number of beams	4
Beam separation	300 mm
Items supplied	Passive unit
Mechanical data	
Dimensions	See dimensional drawing
Housing cross-section	30.7 mm x 34 mm
Material	
Housing	Aluminum extruded profile
Front screen	Polycarbonate, scratch-resistant coating
Weight	845 g (± 50 g)
Ambient data	
Enclosure rating	IP65 (IEC 60529) IP67 (IEC 60529)
Ambient operating temperature	-30 °C +55 °C
Storage temperature	-30 °C +70 °C
Air humidity	15 % 95 %, Non-condensing

5 g, 10 Hz ... 55 Hz (IEC 60068-2-6)

10 g, 16 ms (IEC 60068-2-27)

Vibration resistance


Shock resistance

Classifications

eCl@ss 5.0	27272703
eCl@ss 5.1.4	27272703
eCl@ss 6.0	27272703
eCl@ss 6.2	27272703
eCl@ss 7.0	27272703
eCl@ss 8.0	27272703
eCl@ss 8.1	27272703
eCl@ss 9.0	27272703
eCl@ss 10.0	27272703
eCl@ss 11.0	27272703
eCl@ss 12.0	27272703
ETIM 5.0	EC001832
ETIM 6.0	EC001832
ETIM 7.0	EC001832
ETIM 8.0	EC001832
UNSPSC 16.0901	46171620

Dimensional drawing (Dimensions in mm (inch))

Passive unit for small sensing range (fiber deflection)



PSN02-2301 | deTem

SAFETY MULTIBEAM SENSORS

Recommended accessories

Other models and accessories -> www.sick.com/deTem

	Brief description	Туре	Part no.
Muting access	sories		1
0.	Sensor bracket G6 and P250	BEF-2KHAAAKU1	2113145
	Universal holder for round steel arms and muting arms, for mounting sensors or reflec- tors	BEF-KHS-N01	2044953
	Muting arm bracket	Muting arm bracket	2106455
	Muting arm, long	Muting arm, long	2111923
	Muting arm, short	Muting arm, short	2111924
Terminal and	alignment brackets		
Red Co	4 pieces, FlexFix bracket for 2 devices (e.g. sender and receiver), can be aligned \pm 15 °, including M5 screw, plastic	BEF-1SHABPKU4	2066614
191	4 pieces, QuickFix bracket for 2 devices (e.g. sender and receiver), plastic	BEF-3SHABPKU4	2098710

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

