

ZCKY71TK

Limit switch lever, Limit switches XC Standard, ZCKY, forked arm with rollers 1 track, -40...70 °C



ZCKY71

Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch lever
Device short name	ZCKY
Product Compatibility	XCKJ
Associated head	ZCKE09
Movement of operating head	Rotary
Type of operator	Stay put forked arm with rollers stay put thermoplastic 1 track)
Type of approach	Lateral approach

Complementary

Switch actuation	By specific cam
Positive opening	Without

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C) standard environment -40...158 °F (-40...70 °C) low temperature
Ambient air temperature for storage	-40...158 °F (-40...70 °C) standard environment -40...158 °F (-40...70 °C) low temperature
Environmental characteristic	Low temperature Standard environment

Ordering and shipping details

Category	US1000T22411
Discount Schedule	000T
GTIN	3389118129962
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	2.56 in (6.5 cm)
Package 1 Length	1.77 in (4.5 cm)
Package 1 Weight	1.06 oz (30.0 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Circularity Profile	No need of specific recycling operations
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------