



Main

Device short name	C
Head type	Type C turret head rotary lever
Provided equipment	Receptacle
Series name	Heavy duty

Complementary

Line Rated Current	10 A
Body material	Zinc alloy
Cable entry	0.5 in (12.70 mm) NPT conduit entry
Contact code designation	A600 R300
Contact form	Form ZZ DPDT-DB
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Contacts type and composition	2 NO/2 NC
Maximum displacement angle	90 °
Pilot light	without pilot lamp
Switch actuation	CW and CCW
Tilting angle	45 °
Torque Value	3 lbf.in (0.34 N.m)

Environment

Ambient air temperature for operation	-20...185 °F (-29...85 °C)
Environmental characteristic	Hazardous location
Product Certifications	UL Listed[RETURN]CE[RETURN]CSA


Ordering and shipping details

Category	US10DS121499
Discount Schedule	0DS1
GTIN	785901711551
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.99 in (17.742 cm)
Package 1 Width	2.75 in (6.985 cm)
Package 1 Length	17.74 in (45.064 cm)
Package 1 Weight	2.50 lb(US) (1.134 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------