



#### Main

Device short name	C
Series name	Heavy duty

#### Complementary

Line Rated Current	10 A
Body material	Zinc alloy
Contact code designation	Q600 A600
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Localisation on device	Viton seal kit
Maximum displacement angle	90 °
Specificity of operator	Low differential
Switch actuation	CW and CCW
Tilting angle	5 °
Torque Value	4 lbf.in (0.45 N.m)
Tripping angle	2 °

#### Environment

Ambient air temperature for operation	-20...185 °F (-29...85 °C)
Product Certifications	CE[RETURN]CSA[RETURN]UL Listed


#### Ordering and shipping details

Category	US10DS121499
Discount Schedule	0DS1
GTIN	785901915546
Returnability	No
Country of origin	MX

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.16 in (25.806 cm)
Package 1 Width	4.00 in (10.16 cm)
Package 1 Length	25.81 in (65.548 cm)
Package 1 Weight	20.00 oz (566.99 g)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
For all Reach Rohs enquiries contact us at	<a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>

## Contractual warranty

Warranty	18 months
----------	-----------