

# Actuator

46-

2134.3150.000

Distribution by  
Newark



<https://newark.eao.com/p/46-2134.3150.000>

Your product:

---



## 46-2134.3150.000 Actuator

### FRONT

|                       |           |
|-----------------------|-----------|
| Front dimension:      | Ø 29,5 mm |
| Front bezel material: | Metal     |
| Front bezel colour:   | Silver    |
| Front form:           | round     |

### MOUNTING

|                   |           |
|-------------------|-----------|
| Mounting cut-out: | Ø 22.3 mm |
| Design:           | raised    |

### OPERATING-/INDICATION PART

|                    |                  |
|--------------------|------------------|
| Lens shape:        | flush            |
| Lens material:     | Plastic          |
| Lens illumination: | non illuminative |
| Lens colour:       | Green            |
| Lens optics:       | opaque           |

### ELECTRICAL CHARACTERISTICS

|                   |    |
|-------------------|----|
| Protection class: | II |
|-------------------|----|

### MECHANICAL CHARACTERISTIC

|                    |                                  |
|--------------------|----------------------------------|
| Weight:            | 0.033 kg                         |
| Tightening torque: | 2 ... 3 Nm (17.7 ... 26.6 Lb-in) |

**Switching action:** Maintained

**Mechanical lifetime:** 500 000 cycles of operation

#### AMBIENT CONDITION

**Operating temperature:** – 25 °C ... + 55 °C

**Shock resistance:** 50g, 11ms (EN-IEC 60068-2-27)

**Vibration resistance:** 5g f= 2...500Hz (EN-IEC 60068-2-6)

**Climate resistance:** +25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)

**IK front protection:** IK03

**IP front protection:** IP65

#### CERTIFICATE

**Standards:** CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508

**Conformities:** CE

#### OTHER

**Housing material:** Plastic

**Short Description:** Actuator, Ø 22.3 mm, Ø 29,5 mm, flush, non illuminative, Green, Plastic, opaque, round, Silver, Metal, Maintained, IP65, IK03

**Housing colour:** Black

**max. number of switching elements:** 6

**Dimension drawings:**

